



M-A020

FEATURES

- ❖ Factory tested
- ❖ Corner Unit
- ❖ Polished Finish
- ❖ Phone
- ❖ Auxiliary RCA input
- ❖ Steam Aromatherapy Cup
- ❖ Towel bar & Accessory rack
- ❖ Blue tinted doors and solid black walls
- ❖ Foot Massage
- ❖ Body Massage Jets
- ❖ Rainfall Shower Head
- ❖ Mood light
- ❖ Sliding Doors
- ❖ Hand-held Shower w/ Height-Adjustable Bracket
- ❖ Adjustable Time & Steam Temperature Settings
- ❖ Control Panel with Remote
- ❖ Circulation Fan
- ❖ Tempered Glass
- ❖ 2.5kW Self-Cleaning Steam Generator
- ❖ Folding Seat
- ❖ Pressure Balance Valve (optional extra)
- ❖ FM Transmitter (optional extra)

TECHNICAL INFORMATION

- **Materials:** Acrylic, Aluminum, Tempered Glass
- **Power Supply:** 220V
- **Steam Ready:** 2-5 MIN
- **Dimensions:** 37 x 37 x 87 IN

ELECTRICAL INFORMATION

- 1 dedicated 12-2 line for steam (line 1, line 2, and ground)
- 220 volt, 20 amp GFCI breaker
- There is a length of wire from the control box supplied to connect to power source.

PLUMBING REQUIRMENTS

- The unit is equipped with hot and cold, metal braided 1/2 inch 3 foot long water supply hose with national pipe thread.
- Need to install hot and cold shutoffs with 1/2 inch -male national pipe thread (not included).
- Supply hoses are to connect from the faucet manifold on the unit to the shutoff valves.
- All water jet features are pre plumbed with reinforced braided flexible supply hose
- All fixtures and fittings must be checked for tightness as they may have been loosened during transport.
- Access panel area recommended.
- **Note:** The flexible drain hose included with this unit is for installation into a floor drain only. Substituting the existing drain setup for a setup of the installers' choice will not void the warranty of the unit as long as there is no evidence of misuse or damage to the base. If the substitute drain system is used, a 3/8 in stub must be added to the main shower drain line to connect the steam generator's automatic flushing drainage hose.
Please call the manufacturer for updated drain info 1-866-STEAM-61

GENERAL INFORMATION

- Units come broken down in panels and are assembled with screws, nuts and bolts on site. All seams and joints are to be caulked with 100% silicone at room temperature (no latex caulking)
- **Note:** It is advised to have base onsite before preparing drain location. All shower bases need to be leveled in its final resting position, mark the placement, then pull base out and begin assembly.
- Access panel near controls panel and jets recommended.
- **Manufacturer reserves the right to change specs or features at anytime. Please check to confirm details. 1-866-783-2661**

